



MATERIALS AND FINISHES

- BODY BRASS
PLATED GOLD 1 MICROINCHS MIN.
- CENTER CONTACT BRASS
PLATED GOLD 10 MICROINCHS MIN.
- INSULATOR TEFLON
- JAM NUT BRASS
PLATED GOLD 1 MICROINCHS MIN.
- LOCK WASHER PHOSPHOR BRONZE
PLATED GOLD 1 MICROINCHS MIN.



RECOMMENDED PCB LAYOUT

MIL-STD-348A FIG. 311-1	PERFORMANCE SPECIFICATION
SPECIFICATION	DESCRIPTION

<p>NEW RELEASED EC NO: URF200520230 DRWNLN CHKD: APPR:MHUANG</p>	<p>2004/12/27</p>	<p>QUALITY SYMBOLS</p> <p>▽=0</p> <p>⊕=0</p>	<p>GENERAL TOLERANCES (UNLESS SPECIFIED)</p> <table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.25</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.13</td> <td>± ---</td> </tr> </tbody> </table> <p>ANGULAR ± 2 °</p>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.25	± ---	1 PLACE	± 0.13	± ---	<p>DIMENSION STYLE</p> <p>MM/IN</p>	<p>SCALE</p> <p>2.5:1</p>	<p>DESIGN UNITS</p> <p>METRIC</p>	<p>THIRD ANGLE PROJECTION</p>
		mm	INCH																			
	4 PLACES	± ---	± ---																			
	3 PLACES	± ---	± ---																			
2 PLACES	± 0.25	± ---																				
1 PLACE	± 0.13	± ---																				
<p>REV</p>	<p>DESCRIPTION</p>	<p>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</p>	<p>DRAWN BY</p> <p>EVITA</p>	<p>DATE</p> <p>2004/12/07</p>	<p>TITLE</p> <p>50 OHM SMB VERTICAL PCB MOUNT JACK RECEPTACLE SMB-J/PCB</p>	<p>MOLEX INCORPORATED</p>	<p>SHEET NO.</p> <p>1 OF 1</p>															
<p>SIZE</p> <p>A3</p>	<p>MATERIAL NO.</p> <p>73396-0380</p>	<p>APPROVED BY</p> <p>MISEN</p>	<p>DATE</p> <p>2004/12/07</p>	<p>DOCUMENT NO.</p> <p>SD-73396-038</p>	<p>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</p>																	