

Color: ■ silver-colored      Similar to illustration

Technical data	
Suitable	without button frame
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	300 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Height	22 mm
Width	22 mm
Depth	0.09 mm
Marking surface	22 x 22 mm

Mechanical data	
Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	silver-colored
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent; foamed
Halogen-free	Yes
Weight	92 g
Fire load	0 MJ





Environmental requirements		
Ambient temperature (storage)		≥+22 °C
Ambient temperature (operation)		-30 ... +130 °C
Relative humidity		40 ... 50 %

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4055143426442
Customs tariff number		39191080888

Product classification		
UNSPSC		55121718
eCl@ss 10.0		27-40-06-29
eCl@ss 9.0		27-40-06-29
ETIM 9.0		EC001288
ETIM 8.0		EC001288
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 210-847		

Documentation				
Operating Instructions				
210-852 Information on handling print material	1		pdf	
	28.08.2020		1004.72 KB	

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)