Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
  - Accessory
  - M5
  - Guided M8
  - M8
  - M10.5
  - M12 (A)
  - M12 (B)
  - M12 (D)
  - M12 (I)
  - M12 (K)
  - M12 (L)
  - M12 (S)
  - M12 (T)
  - M12 (X)
  - M23
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





M12X-08PFFT-EE0003

Operating Temperature: -55°C ~ +125°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: N/A
Certificate: N/A

You must login first for view the price


Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type | Search



M Series,...	M Series,...	M Series,...	M Series,...	M Series, M12, A...	M Series, M12, A...
APPM-AAAFA012-... N/A	APPM-AAAFA012-... N/A	APTM-BMZFA012-... N/A	CAP-WBDFSMA1 -40°C ~ +105°C	MSAS-08BMMA-... -40°C ~ +105°C	MSAS-08BMMA-... -40°C ~ +105°C
− 0 +	− 0 +	− 0 +	− 0 +	− 0 +	− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **0.5A**	Connector Type **SMT**
Shielded **Plastic, Non-shielded**	No. of Contacts **08**
Connector Gender **Female**	Backshell **N/A**
Mating Style **N/A**	IP Rating **Non-waterproof**
Assembly Style **SMT 180°**	

More Options

People Also Bought



M12X-08PFFT-... | DC-03BFFA-QL8LNP | 1CD-12BFFM-SL6A05 | 1CD-10BFFM-SL6A10 | 8P-03BFFM-SR7A02

Downloaded from Arrow.com.