
Part Number : 1731120648
Product Description : FCT Stamped Contact, Male, Crimp, 0.60µm Gold Mating Plating, 28-24 AWG, 2,000 pieces on reel
Series Number : 173112
Status : Obsolete
Product Category : D-Sub Contacts
Engineering Part Number : P110-06V-5876



Obsolete

Documents and Resources

Specifications

1731120004-PK-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	D-Sub Contacts
Series	173112
Description	FCT Stamped Contact, Male, Crimp, 0.60µm Gold Mating Plating, 28-24 AWG, 2,000 pieces on reel
Comments	Packaging Detail: 2,000 pieces on a reel
Contact Type	Stamped Crimp
Product Name	FCT Products
Type	Standard Density
UPC	191128757546

Physical

Gender	Male
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Net Weight	0.100/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	0.600µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp
Wire Size (AWG)	24, 26, 28

Mates With / Use With

Use with Part(s)

Description	Part Number

Obsolete

Downloaded from Arrow.com.

Use With	FCT High-Density Connectors

This document was generated on Aug 16, 2026

Obsolete

Downloaded from Arrow.com.