Part Number : 436450608
Product Description : Micro-Fit 3.0 Receptacle Housing, Single Row, 6 Circuits, UL 94V-0, Low-Halogen Since Inception, Black
Series Number : 43645
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

436450608_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

430250000-AS-000.pdf

PK-43645-001-001.pdf

436500001-PS-JA-000.pdf

436500001-PS-KO-000.pdf

436500001-PS-SP-000.pdf

PS-43650-001.pdf

430450005-TS-000.pdf

430450007-TS-000.pdf

TS-43045-001-001.pdf

TS-43045-002-001.pdf

TS-43045-003-001.pdf

TS-46235-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC

Downloaded from Arrow.com.

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	43645
Description	Micro-Fit 3.0 Receptacle Housing, Single Row, 6 Circuits, UL 94V-0, Low-Halogen Since Inception, Black
Application	Wire-to-Board, Wire-to-Wire
Comments	Halogen Free/Low Halogen since inception
Component Type	Receptacle
Product Name	Micro-Fit 3.0
UPC	883906111625

Agency

CSA	LR19980

Downloaded from Arrow.com.

UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.664/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Single Row Plug Housings	43640
Micro-Fit TPA Single Row Plug Housings	200875
Micro-Fit 3.0 Single Row Headers	43650
Micro-Fit 3.0 Male-to-Micro-Fit 3.0 Male Off-the-Shelf (OTS) Cable Assemblies	214752
Micro-Fit 3.0 Male-to-Pigtail Off-	214753

Downloaded from Arrow.com.

the-Shelf (OTS) Cable Assemblies	

Use with Part(s)

Description	Part Number
Micro-Fit 3.0 Female Crimp Terminals	43030
Micro-Fit Reduced Mating Force Female Crimp Terminals	46235
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female	214760
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Pigtail	214761

Downloaded from Arrow.com.