

U

(M) SKETCH 9932
ISSUE 1

REPLACES

SR 4502

55. 44

٢٢٥

137M3

55.

6 MW

33

CHECK

5

MAY 1964

✓ 11

下


55 CHE

MAY

ப.

FORMTEK

二



NOTE
 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA		SCALE FULL
OPERATING FORCE - - - - - 2 1/2 OZ MAX	CONTACT ARRANGEMENT		DO NOT SCALE PRINT
RELEASE FORCE - - - - - 1/4 OZ MIN	S.P.D.T.		UNLESS OTHERWISE SPECIFIED
DIFFERENTIAL TRAVEL - - - - - .003 - .020	L96		DIMENSIONS ARE IN INCHES
OVERTRAVEL - - - - - .093 MIN	15A 125, <u>250</u> OR 480 VAC		TOLERANCES ARE:
	1/2A 125 VDC, 1/4A 250 VDC		ONE PLACE (.01) ±.005
	1/8HP 125 VAC, 1/4HP <u>250</u> VAC		TWO PLACE (.00) ±.015
	L288	  	THREE PLACE (.000) ±.005
	L299		ANGLES ±
	L306		
	16A 250V ~ T85 5E4		WEIGHT .073 LB.