

28061

[Products](#) > [Controls and Monitors](#) > [Operator Controls](#) > [Hour Meters](#) > [ac Hour Meters](#) > [28100 Series](#) > **28061**

Overview

Honeywell Standard ac Hour Meter, rectangle opening, retainer mounting, 0.25 in bent blade termination, 100K hours, 22 Vac to 26 Vac operating voltage, 24 V, 60 Hz, faceplate: bla

[View More](#)



Technical Specifications

Product Type	Standard ac	Function	Hour Meter
Appearance	Rectangle	Mounting	Retainer
Voltage	22 Vac to 26 Vac	Volts ac	24 Vac
Frequency	60 Hz	Hours	100K
Logo Top	Hour Glass	Logo Bottom	Hours 1/10

[View More](#)

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
True Time Stamp - Hour Meters	Case Study	English	345KB
Hour Meters Line Guide	Product Line Guide	English	571KB
Industrial Product Line Card	Line Card/Selection Chart	English	571KB
Sensors and Switches for Potential Medical Applications	Application Note	English	374KB

[View More](#)

Applications

- Control panels
- Medical applications

view all 28061 literature

view distributor inventory

sample request

email support

get support

email sales

find a distributor

email this page

NAVIGATION LINKS

- HOME PAGE
- PRODUCTS
- DISTRIBUTOR INVENTORY
- INDUSTRIES
- SUPPORT

DISTRIBUTOR LINKS

- ECOM LOGIN
- LEARN CENTER
- REQUEST ACCESS TO ECOM
- SALES/AD PORTAL LOGIN
- SALES/AD PORTAL ACCESS REQUEST

LANGUAGE

English

SOCIAL MEDIA



SITE INFORMATION

NEWS & EVENTS

SAMPLE REQUEST

PRIVACY STATEMENT

ABOUT US

SUPPLIER MICROSITE

SITEMAP

TERMS & CONDITIONS

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.