









基板取付寸法 (奇数ピン)
MOUNTING LAYOUT (ODD PIN)



基板取付寸法 (偶数ピン)
MOUNTING LAYOUT (EVEN PIN)

NO.	DESCRIPTION	PART NO.	QTY	MATERIAL	DRW NO.	REMARKS
1	SLIDER		1	HEAT RESISTING PLASTIC		UL94V-0 COLOR:NATURAL
2	INSULATOR		1	HEAT RESISTING PLASTIC		UL94V-0 COLOR:NATURAL
3	CONTACT		N	PHOS-BRONZE		t=0.2 AU

極数 NO. OF POS.	A	B	C	D
6	7.5	6.9	2.5	3.6
7	8.0	7.4	3.0	4.1
8	8.5	7.9	3.5	4.6
9	9.0	8.4	4.0	5.1
10	9.5	8.9	4.5	5.6
11	10.0	9.4	5.0	6.1
12	10.5	9.9	5.5	6.6
13	11.0	10.4	6.0	7.1
14	11.5	10.9	6.5	7.6
15	12.0	11.4	7.0	8.1
16	12.5	11.9	7.5	8.6
17	13.0	12.4	8.0	9.1
18	13.5	12.9	8.5	9.6
19	14.0	13.4	9.0	10.1
20	14.5	13.9	9.5	10.6
21	15.0	14.4	10.0	11.1
22	15.5	14.9	10.5	11.6
23	16.0	15.4	11.0	12.1
24	16.5	15.9	11.5	12.6
25	17.0	16.4	12.0	13.1
26	17.5	16.9	12.5	13.6
27	18.0	17.4	13.0	14.1
28	18.5	17.9	13.5	14.6
29	19.0	18.4	14.0	15.1
30	19.5	18.9	14.5	15.6

※この表は1ページ目のみ適用
※THIS CHART IS APPLICABLE TO SHEET-1 ONLY.

注 記
NOTE

① コンタクトテールの最大浮き0.1mmとする。
CONTACT TAIL
HEIGHT SHALL BE 0.1mm MAX.


② 適用FPC, FFC寸法は1か2を選択のこと。
SELECT AN APPLICABLE FPC, FFC
FROM 1 OR 2.

※この注記の1～2は1ページ目のみ適用
※THIS NOTES 1 TO 2 ARE APPLICABLE TO SHEET-1 ONLY.

ROHS規制対応
COMPLIANT WITH
ROHS REGULATIONS



	FPC		FFC	
	1	2	1	2
M	0.5±0.12	0.5±0.1	0.5±0.1	0.5±0.08
P	0.5±0.02	0.5±0.05	0.5±0.03	0.5±0.05
B	B±0.03	B±0.05	B±0.03	B±0.05
W	W±0.07	W±0.07	W±0.07	W±0.07
WD	0.35 ^{+0.04} _{-0.03}	0.35±0.05	0.3 ^{+0.05} _{-0.02}	0.3 ^{+0.05} _{-0.02}

適用FPC, FFC寸法
APPLICABLE FPC, FFC





TOLERANCE / 一般公差 (S)		PRODUCT SPEC / 製品規格					
10≤ X < 30 30≤ X	X < 10 ±0.2	UNIT mm	ANGLE 3RD	A	DCN20601	2020/06/12	A. MURATA
	X < 30 ±0.25			O	EDN-457	2007/06/18	N. KITAGAWA
	X ±0.3			NO.	EDN/DCN	DATE	ISSUE
ANGLE / 角度 ±3°		SCALE 10:1	DATE 2007/06/18	PART NAME / 品名 SERIES 6214 FPC FFC ASSY ST SMT 0.5mmPITCH WITHOUT ANCHOR PLATE			
DRAWN LI	DESIGNED N. KITAGAWA	CHECKED	APPROVED T. SATOH	PART NO. / 製番 04 6214 0XX 110 846 +			
DWG NO. / 図番 BJS 6214146				SHEET/REV 1/2 A			


KYOCERA




SECT. E-E
(6~24P)




SECT. E-E
(25~30P)



SECT. F-F (S=5:1)



REEL DIMENSION (S=1:5)



NO.	DESCRIPTION	PART NO.	QTY	MATERIAL	DRW NO.	REMARKS
1	CONNECTOR	04 6214 0XX 110 846 +	1000			00 6214 0XX 110 846 +
2	EMBOSSED TAPE		1	POLYSTYRENE		
3	TOP COVER TAPE		1	POLYSTYRENE		
4	REEL		1	POLYSTYRENE		


極数 NO. OF POS.	A	B	C	D
6	7.5	—	16.0	22.4
7	7.5	—	16.0	22.4
8	7.5	—	16.0	22.4
9	11.5	—	24.0	30.4
10	11.5	—	24.0	30.4
11	11.5	—	24.0	30.4
12	11.5	—	24.0	30.4
13	11.5	—	24.0	30.4
14	11.5	—	24.0	30.4
15	11.5	—	24.0	30.4
16	11.5	—	24.0	30.4
17	11.5	—	24.0	30.4
18	11.5	—	24.0	30.4
19	11.5	—	24.0	30.4
20	11.5	—	24.0	30.4
21	11.5	—	24.0	30.4
22	11.5	—	24.0	30.4
23	11.5	—	24.0	30.4
24	11.5	—	24.0	30.4
25	14.2	28.4	32.0	38.4
26	14.2	28.4	32.0	38.4
27	14.2	28.4	32.0	38.4
28	14.2	28.4	32.0	38.4
29	14.2	28.4	32.0	38.4
30	14.2	28.4	32.0	38.4

※この表は2ページ目にのみ適用
※THIS CHART IS APPLICABLE TO SHEET-2 ONLY.

注記
NOTE


1. 梱包数量 : 1000 個/リール
PACKING QUANTITY : 1000 ea/reel

2. 納入時のリール巻方向
DIRECTION OF REEL



3. 引出し方向

USER DIRECTION OF FEED



4. 型番
P/N

04 6214 0XX 110 846 +

極数
NO. OF POS.

バリエーション
VARIATION

1: 金具なし
WITHOUT ANCHOR PLATE

めっきコード

PLATING CODE
846+: AU (SELECTIVE)

※この注記の1~3は2ページ目にのみ適用

※THIS NOTES 1 TO 3 ARE APPLICABLE TO SHEET-2 ONLY.

TOLERANCE / 一般公差 (S)		PRODUCT SPEC / 製品規格													
X <10 10 ≤ X <30 30 ≤ X	±0.2 ±0.25 ±0.3	UNIT		ANGLE		REFER TO SHEET		1/2							
		mm		3RD		NO.		EDN/DCN	DATE	ISSUE	CHECKED	APPROVED			
		SCALE		DATE		PART NAME / 品名									
ANGLE / 角度		±3°		2 : 1		2007/06/18		EMBOSS TAPE ASSY FPC FFC ASSY ST SMT							
DRAWN	DESIGNED	CHECKED		APPROVED		PART NO. / 型番									
LI	N. KITAGAWA			T. SATOH		04 6214 0XX 110 846 +									
						DWG NO. / 図番				SHEET/REV					
						BJS 6214146				2/2 A					

KYOCERA

ROHS規制対応
COMPLIANT WITH
ROHS REGULATIONS