


REV.	DATE	ECR NO.	DESCRIPTION
NC	08/25/09	XXXXXX	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
						DRAWN	CW	08/25/09										
						CHECKED												
6	RETAINER RING	BERYLLIUM COPPER	NATURAL	2						PART DESCRIPTION								
5	GASKET	SILICONE	RED	2						SMA PLUG TO PLUG ADAPTOR								
4	CONTACT PIN	BRASS	GOLD	1														
3	INSULATOR	PTFE	NATURAL	2						PART NO.								
2	SHELL	STAINLESS STEEL	PASSIVATED	2														
1	BODY	STAINLESS STEEL	PASSIVATED	1						132168SS								
	DESCRIPTION	MATERIAL	FINISH	QTY														
						CAD FILE		C:/CONNEX/132168SS.DWG		DWG. NO.	132168SS.DWG		REV.	NC	SIZE	A	SCALE	NA