



Part Number : [1110401104](#)
Product Description : QSFP+-to-QSFP+ Cable Assembly, 30 AWG, 1.0m Length
Series Number : 111040
Status : Active
Product Category : High-Speed I/O Cable Assemblies



Documents & Resources

Drawings
[1110401104_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains TBBA per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	111040
Description	QSFP+-to-QSFP+ Cable Assembly, 30 AWG, 1.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP+-to-QSFP+
Product Name	QSFP Plus,QSFP+
Type	Pluggable
UPC	883906912994

Agency

UL	E72548
----	--------

Electrical

Data Rate	10.0 Gbps
Impedance	100Ω

Physical

Cable Bundling	None
Cable Length	1.0m
Circuits (Loaded)	MSA
Gender	Plug
Lock to Mating Part	Yes
Net Weight	123.000/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Round
Wire Size (AWG)	30

Mates With / Use With

Mates with Part(s)

Description	Part Number
iPass I/O Right-Angle Surface Mount Receptacles	<u>75586</u>

Use with Part(s)

Description	Part Number
QSFP+ Cage Assemblies, Light Pipes, and Heat Sinks	<u>74750</u>
QSFP+ 1x3 Ganged Cage Assemblies and Heat Sink Clips	<u>74768</u>
QSFP+ Ganged Cages and Light Pipe Assemblies	<u>74769</u>

This document was generated on Apr 26, 2025