

6

5

4

3




2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/5/07	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Nylon 6T, rated UL 94V-0

Insulator color: Ivory

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 260°C. for 5 sec.



A= .049 [1.25] X NO. OF SPACES
B= .049 [1.25] X NO. OF SPACES +.114 [2.90]
C= .049 [1.25] X NO. OF SPACES +.173 [4.40]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

HIROSE DF13-1.25mm WAFER XHP SMT 180°

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES
X .10 ±.10
XX .020 ±.015
XXX .015 ±.010

APPROVALS

DATE

DRAWN

SS

11/5/07

CHECKED

APPROVED

TITLE

HIROSE DF13-1.25mm WAFER XHP SMT 180°

SIZE

X

PART NO. 125SH-C-XX-TS-SMT-TR

REV. -



REF:

SCALE: NTS

SHEET 1 OF 2

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION HISTORY				

APPROVED: _____
 DATE: _____ TITLE: _____



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]		TOLERANCES: EXCEPT AS NOTED	
INCHES		HOLES	
X	± .10	ØX	± .10
XX	± .020	ØXX	± .015
XXX	± .015	ØXXX	± .010
APPROVALS		DATE	
DRAWN	SS	11/5/07	
CHECKED			
APPROVED			
TITLE		HIROSE DF13-1.25mm WAFER XXP SMT 180°	
909 Rahway Avenue, Union, NJ 07083		Phone: 908-687-5000 Fax: 908-687-5710	

SIZE	PART NO.	SCALE	SHEET
X	125SH-C-XX-TS-SMT-TR	NIS	2 OF 2
REV.			