

Search:

Go

[Connectors](#)[Sockets /
Edgecards](#)[Cable
Assemblies](#)[Antennas](#)[Fiber Optic
Products](#)[Printed Circuit
Products](#)[Automation /
Industrial](#)[Lighting
Products](#)

Home:

Part Number: 64335-1021

Series image - Reference only

Status:

Contact Molex

Series:[64335](#)**Category:**

Molex Parts

Go to **Part Detail**[CHECK DISTRIBUTOR INVENTORY](#)[Add to My Parts](#)Questions on Product Environmental Compliance? Email productcompliance@molex.com[EU RoHS](#) : ELV and RoHS Compliant[China RoHS](#) : ☐[REACH SVHC](#) : Not Reviewed[Low-Halogen Status](#) : Not Reviewed

Product Compliance Statement

Part Detail[SHOW ALL](#)**General**

Status	Contact Molex
Category	Molex Parts
Series	64335
UPC	883906127510

Physical

Net Weight	58.956/g
------------	----------

Solder Process Data

Duration at Max. Process Temperature (seconds)	35
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info**Application Tooling**[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)**Molex Connectors**

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

Other Products

- Fiber Optic Products
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies
- Woodhead Electrical
- Solid State Lighting

Resources

- Contact Us
- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

Company Info

- About Us
- Careers
- ecocare
- Investors
- Press Room
- Shows & Events
- Supplier Portal

Other Info

- Feedback
- Help
- Legal Disclaimer
- View Mobile Site
- Privacy Policy
- Sitemap

Stay Connected with Molex:

□□□

