
Part Number : 1300062436
Product Description : Mini-Change A-Size Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow TPE Cable, 3.0m (9.84') Length
Series Number : 130006
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 104006K12M030



Documents and Resources

Drawings

1300062436_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; diphenyl(2,4,6-trimethylbenzoyl)phosphine oxide per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow TPE Cable, 3.0m (9.84') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	78172549482

Agency

UL	E152210

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V

Physical

Cable Diameter	10.92mm (.430")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change

Downloaded from Arrow.com.

Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	231.000/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	16

Downloaded from Arrow.com.