Part Number : 1062920505
Product Description : MMC Female-to-(2) MPO Female Fiber Optic Breakout Patch Cord, Singlemode, 16 Fiber BIF Plenum Cable, 5.0m Length, Yellow Cable
Series Number : 86170
Status : Active
Product Category : Fiber Optic Cable Assemblies



Documents and Resources

Drawings

1062920505_sd.pdf

Specifications

1062920301-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86170
Description	MMC Female-to-(2) MPO Female Fiber Optic Breakout Patch Cord, Singlemode, 16 Fiber BIF Plenum Cable, 5.0m Length, Yellow Cable
Connector to Connector	MMC-to-(2) MPO
Mode	Singlemode
Product Name	MMC,MPO
UPC	198282258834

Physical

Boot Type	Straight
Cable Length	5.0m
Cable Size	2.50mm, 3.00mm
Fiber (Core/Cladding)	9/125µm
Net Weight	1.000/g
Single Ended	No
Wire/Cable Type	16 Fiber Bend-insensitive Plenum

Downloaded from Arrow.com.