


DRAWING NO.
30022799

ITEM NO.	CATALOG NO.	WIRE RANGE (AWG)	STUD SIZE	MAX. INSULATION DIAMETER	DIMENSIONS								INSTALLATION TOOLING		WIRE STRIP LENGTH	REV	DATE	DESCRIPTION	ECO	BY	C'H'K.									
					B	C	K DIA.	L	N	O.D.	T	Z MIN.	NON-RATCHET	RATCHET		A	12/02/2011 00:00:00 AM	SALES DRAWING UPDATED --	26289	AD	MA									
603400	YAV10H	12-10	8-10	.192 [4]	.31 [8]	.38 [10]	.20 [5]	1.05 [27]	.19 [5]	.21 [5]	.06 [2]	.28 [7]		 MRE1022B MR8-G98, MR8-9Q, Y8MRB-1 MR20, M8ND WITH N10HT DIE OR N10HT-24 DIE	7/16"															
603405	YAV10H2		5/16"		.31 [8]	.53 [13]	.33 [8]	1.24 [31]	.27 [7]	.21 [5]	.04 [1]	.39 [10]																		
603425	YAV10H25		6-8		.31 [8]	.31 [8]	.17 [4]	1.00 [25]	.16 [4]	.21 [5]	.07 [2]	.26 [7]																		
603410	YAV10H3		1/4"		.31 [8]	.47 [12]	.27 [7]	1.17 [30]	.23 [6]	.21 [5]	.05 [1]	.36 [9]																		
603415	YAV10H4		3/8"		.31 [8]	.55 [14]	.40 [10]	1.24 [31]	.28 [7]	.21 [5]	.04 [1]	.44 [11]																		
603435	YAV14H	16-14	8-10	.150 [4]	.25 [6]	.31 [8]	.20 [5]	.92 [23]	.16 [4]	.16 [4]	.04 [1]	.26 [7]		 MRE1022B MR8-G98, MR8-9Q, Y8MRB-1 MR20, M8ND WITH N14HT-5 DIE, N10HT-24 DIE, OR N14HT DIE	1/4"															
603440	YAV14H1		6-8		.25 [6]	.31 [8]	.17 [4]	.92 [23]	.16 [4]	.16 [4]	.04 [1]	.26 [7]																		
603445	YAV14H2		1/4"		.25 [6]	.42 [11]	.27 [7]	1.11 [28]	.25 [6]	.16 [4]	.03 [1]	.36 [9]																		
10019911	YAV14H5		4-5		.25 [6]	.31 [8]	.15 [4]	.92 [23]	.16 [4]	.16 [4]	.04 [1]	.26 [7]																		
603458	YAV14H65		8-10		.25 [6]	.31 [8]	.21 [5]	.92 [23]	.16 [4]	.16 [4]	.04 [1]	.26 [7]																		
603460	YAV18H	22-18	8-10	.120 [3]	.25 [6]	.31 [8]	.20 [5]	.88 [22]	.16 [4]	.13 [3]	.03 [1]	.28 [7]		 MRE1022B MR8-G98, MR8-9Q, Y8MRB-1 MR20, M8ND WITH N14HT-5 DIE OR N14HT DIE																
603465	YAV18H1		6-8		.25 [6]	.31 [8]	.17 [4]	.88 [22]	.16 [4]	.13 [3]	.03 [1]	.28 [7]																		
603485	YAV18H5		4-6		.25 [6]	.31 [8]	.15 [4]	.88 [22]	.16 [4]	.13 [3]	.03 [1]	.28 [7]																		
603490	YAV18H6		4-6		.27 [7]	.25 [6]	.15 [4]	.89 [23]	.12 [3]	.13 [3]	.04 [1]	.22 [6]																		



NOTES:

1. MATERIAL: SEAMLESS COPPER TUBE
FINISH: TIN PLATED
- 2 THESE TOOLS CRIMP THE CONDUCTOR ONLY; ALL
OTHERS CRIMP THE INSULATION SHROUD AS WELL.
3. ALL DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS,
ROUNDED TO THE NEAREST MILLIMETER
AND ARE FOR REFERENCE ONLY.
4. UL LISTED AND CSA CERTIFIED.
5. USE SUFFIX "BOX" FOR JAR PACKAGING.
6. USE SUFFIX "NK" FOR NICKEL PLATING.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

UNINSULATED RING TERMINAL W/ SHROUD			
ITEM NO: (SEE TABLE)			
CAT. NO: YAV-H-			
DRAWN BY: S.AUGUSTIN	12/02/11		A
CHECKER: E.MARTIN	12/12/11		
DSN APPVL: E.MARTIN	12/12/11		
MFG APPVL: --	--		
QA APPVL: C.ACKERMAN	12/29/11	SCALE: 5:1	A
MKT APPVL: J.SYLVA	12/10/11		
PROD FAM: SMALL COMPRESSION	DRAWING NO		
PROJECT #: --	SIZE		
DOCUMENT TYPE: Sales	C	30022799	A
REL LEVEL: Released		SHEET 1 OF 1	