

CT4299: Fused Probe, 500mA with Locking Tip Cover

DESCRIPTION

SPECIFICATIONS

DOWNLOADS

RELATED PRODUCTS

The CT4299 Fused Probe easily connects to 4 mm sheathed banana plug leads, which are in turn connected to a DMM or other equipment. The small, compact body features an internal, fast acting, ceramic fuse, which can cut power in microseconds during a transient overvoltage, thereby protecting both equipment and more importantly personnel, working in high energy environments. The closer the fuse is to the test point the higher the level of protection.

Available in a black and red pair: **CT4300**

Features:

- Enhanced user safety for high-energy applications. Fast blow fuse will sever the connection in events such as meter failures, transient over-voltages, or arc-flash.
- Small, compact body.
- Rated to 1,000 V CATIII / 600 V CAT IV per IEC/EN 61010-031.
- Fast acting, high quality 500 mA ceramic fuse (maximum fuse current rating).
- Tool-removable locking tip cover.
- Designed to work with 3900 Series DMM tip accessories.
- Easy fuse replacement.
- CE listed – LVD and RoHS 2 compliant.



Click Images For Larger Photo



MODEL #	COLOR	WHERE TO BUY
CT4299-0	Black	
CT4299-2	Red	

22820 SAVI RANCH PARKWAY

YORBA LINDA, CA 92887

CAL TEST ELECTRONICS © 2017



[PRESS RELEASES](#) [SUPPORT](#) [DISTRIBUTOR ACCESS](#) [CATALOG](#) [COMPANY DOCUMENTS](#) [ABOUT](#)