

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



BB-02AMMM-QL8E01

Operating Temperature: -20°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: UL2238, UL50e

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart


 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories


Connector Type ▼ Search



X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

- 0 +


☐



X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

- 0 +


☐



X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

- 0 +


☐



X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

- 0 +


☐



X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 10A	Connector Type Overmolded
Shielded Plastic, Non-shielded	No. of Contacts 02
Connector Gender Male	Backshell Straight
Mating Style Push Lock	IP Rating IP68
Assembly Style N/A	
➕ More Options	

People Also Bought



BB-02AMMM-QL8E01



AB-BB03FL-BBBL-...



AB-BB02HL-BBHL-...



MSAS-04BFFM-...



AB-CD12ML-COML-...