

## Marker for end clamp - UCT-EM (30X5) - 0801505

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for end clamp, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, lettering field size: 30 x 5 mm, Number of individual labels: 24

### Your advantages

- ✓ The UCT-EM (30x5) ... UniCard marking card provides markers for the CLIPFIX 35-5 ... end bracket
- ✓ The sheets provide additional space for project information and function text that can be helpful during further assembly
- ✓ The pin geometry enables the easy mounting and removal of the markers.
- ✓ The markers, which are supplied in uniform sheets, can be marked quickly, easily, and precisely using the card printers
- ✓ Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

**RoHS**

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 673525
GTIN	4046356673525
Weight per Piece (excluding packing)	12.000 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Length (b)	30 mm
Width (a)	5 mm

#### Ambient conditions

# Marker for end clamp - UCT-EM (30X5) - 0801505

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

### General

Color	white
Components	free from silicone and halogen
Material	PC
Flammability rating according to UL 94	V0
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	24
Number of individual labels per row	8
Mounting type	snapped
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 11.0	27281103
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100

## Marker for end clamp - UCT-EM (30X5) - 0801505

### Classifications

#### eCl@ss

eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 9.0	27400629

#### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001288

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

##### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

## Marker for end clamp - UCT-EM (30X5) - 0801505

### Accessories

Ink ribbon cartridge - TMP-RIBBON 110 BK 100 - 0803374



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110/50-TC - 0801384



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

### Magazine

Magazine - TMP-UCT-MAG10 - 0803352



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (30x5)

Magazine - TOPMARK LASER-MAG UCT-A - 0803141



Magazine for the TOPMARK LASER, for accommodating UCT material automatically

Magazine - TOPMARK LASER-MAG UCT-M - 0803143



Magazine for the TOPMARK LASER, for accommodating UCT material manually

## Marker for end clamp - UCT-EM (30X5) - 0801505

### Accessories

#### Printing system accessories

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662



Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge

---

Ink cartridge - BLUEMARK FLUID-CARTRIDGE - 5147421



Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge

---

Ink cartridge - BM ID-CARTR. BK - 1044345



Replacement UV fluid, 23 ml, color: black

---

Ink cartridge - BM ID-CARTR. CY - 1044346



Replacement UV fluid, 23 ml, color: cyan

---

Ink cartridge - BM ID-CARTR. MA - 1044347



Replacement UV fluid, 23 ml, color: magenta

## Marker for end clamp - UCT-EM (30X5) - 0801505

### Accessories

Ink cartridge - BM ID-CARTR. YE - 1044348



Replacement UV fluid, 23 ml, color: yellow

---

Phoenix Contact 2022 © - all rights reserved  
<http://www.phoenixcontact.com>