

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	15AUG2017	SG	MS



STRIP
-2 AS SHOWN



STRIP CONTACT COME OFF TO ASSEMBLY
2000 PCS CONTACTS MOUNTED REEL
REEL TYPE SUBJECT TO ALTERNATION



LOOSE PIECE
-3 AS SHOWN

1. MATERIAL: COPPER ALLOY, TIN PLATED
2. USED FOR SOLAR CABLE: 4mm2/12AWG, 6mm2/10AWG.
3. PLS DON'T TOUCH THE CONTACT DIRECTLY BY HAND WITHOUT ANY PROTECTION.

4 USE ONLY CRIMPING TOOL OF TE CONNECTIVITY TO CRIMP CONTACT. CRIMPING TOOL PN 6-1579014-8 WILL BE USED FOR CRIMPING THE CONTACTS HAVING WIRE SIZE $4.0mm^2+6.0mm^2$.

LOOSE PIECE	2270251-4	100
	2270251-3	1000
STRIP	2270251-2	2000
CONTACT TYPE	PART NUMBER	PACKING UNIT
	FOR ORDER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.5
1 PLC ±0.3
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: COPPER ALLOY
FINISH: TIN

DWN 15AUG2017 SHIRLEY GAO
CHK 15AUG2017 ALEX ZHANG
APVD 15AUG2017 MING SHI
PRODUCT SPEC 108-137077
APPLICATION SPEC 114-137077
WEIGHT -

TE Connectivity

NAME
PIN CONTACT
SOLARLOK PV4-S CONNECTOR
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2270251	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV A

1471-9 (3/13)

Downloaded from Arrow.com.