

POS POLEFIX M 108 VA - Holder



1587068

<https://www.phoenixcontact.com/us/products/1587068>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic holder for Pico off-grid system, fixing for mast Ø 48 mm ... 108 mm, compatible with POS-HP housing sizes 204 mm x 251 mm to 410 mm x 455 mm, and POS PV panel 75, 110, and 190, material: stainless steel

Your advantages

- Internationally certified housing system
- Different housing sizes can be combined with one holder
- Simple 1-person installation of the entire system
- Complete system except own electronics
- Simple supply chain

Commercial data

Item number	1587068
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC04
Product key	ACFDCB
GTIN	4067923142381
Weight per piece (including packing)	7.78 kg
Weight per piece (excluding packing)	7.78 kg
Customs tariff number	73269098
Country of origin	CN

POS POLEFIX M 108 VA - Holder



1587068

<https://www.phoenixcontact.com/us/products/1587068>

Technical data

Notes

Recommendation	Please observe the application note in the download area.
General	Further information and detailed dimensions are available in the download area.
Assembly note	Observe the safety notes in the packing slip prior to mounting. The packing slip is available in the download area.

Safety note

Safety note	WARNING: Risk of crushing due to moving parts. During mounting, make sure not to place your hands between the moving parts. We recommend wearing safety gloves.
-------------	---

Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing series	POS

Dimensions

Dimensions	370 mm x 729.5 mm x 380.9 mm (Angle position 30°, please observe the technical drawing available in the download area)
	370 mm x 567.4 mm x 817.6 mm (Angle position 80°, please observe the technical drawing available in the download area)

Material specifications

Color	silver-colored
Material Basic holder	Stainless steel

Mounting

Mounting type	Mast mounting (Ø 48 mm ... 108 mm)
---------------	------------------------------------

Packaging specifications

Type of packaging	Box packaging
-------------------	---------------

POS POLEFIX M 108 VA - Holder

1587068

<https://www.phoenixcontact.com/us/products/1587068>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

POS POLEFIX M 108 VA - Holder

1587068

<https://www.phoenixcontact.com/us/products/1587068>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com