Part Number : 1300950201
Product Description : Junior Duty Wire Mesh Pulling Grip, Single Weave, Flexible Eye, Mesh Length 0.305m (12.00"), Approximate Break Strength 1859.73kg (4100 lbs)
Series Number : 130095
Status : Active
Product Category : Cable Grips
Engineering Part Number : 35975



Documents and Resources

Drawings

1300950201_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Junior Duty Wire Mesh Pulling Grip, Single Weave, Flexible Eye, Mesh Length 0.305m (12.00"), Approximate Break Strength 1859.73kg (4100 lbs)
Product Name	Junior Duty
Type	Pulling Grip
UPC	78678835975

Agency

CSA	LR32159

Physical

Approximate Break Strength	1859.73kg (4100 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	25.40-31.50mm (1.000-1.240")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.305m (12.00")
Net Weight	156.009/g
Number of Holes	N/A
O-Ring	N/A

Downloaded from Arrow.com.

Thread Size	N/A

Downloaded from Arrow.com.