
Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
  - Accessory
  - Middle Size
  - Mini Size
  - Large Size
  - Standard Size
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





CB-06RMMS-QC8001

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: N/A
Certificate: UL2238, UL50e

You must login first for view the price


Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type ▾ Search



Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **10A**	Connector Type **Receptacle**
Shielded **Plastic, Non-shielded**	No. of Contacts **06**
Connector Gender **Male**	Backshell **Circular**
Mating Style **Push Lock**	IP Rating **IP68**
Assembly Style **Solder**	

More Options

People Also Bought



Downloaded from Arrow.com.