

# YSM28, Uninsulated Parallel Splice For 167,332 - 211,954 cmils

By Burndy  
Catalog # [YSM28](#)



Uninsulated Parallel Splice For 167,332 - 211,954 cmils

## Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

## Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

## Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

## Conductor

Conductor Size	167,332 - 211,954 cmils
Conductor - Copper Str Size	<ul style="list-style-type: none"> <li>• 3/0 AWG</li> <li>• 4/0 AWG</li> </ul>
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Configuration

Connector Type Parallel Splice

## Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.78 in
Package Height	0.000 in
Dimension - Strip Length inch	5/16
Dimension - Length Overall inch	0.88 in

## General

Sub Brand	HYLINK
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	YSM
UPC 12 Digit	781810805855
UPC 14 Digit GTIN	00781810805855
Material	Copper
Plating Type	Tin
UPC	781810805855

## Logistics

Minimum Pack Quantity	1
Carton Quantity	100
Pallet Quantity	46400

## Operational

Temperature Rating	90
--------------------	----

## Product Assets

[Catalog \[English\]](#)