



+ CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)
PROTECTIVE COVER. IPT 16-50mm sq.CABLE D

1-1991225-4
TE Internal Number: 1-1991225-4

- EU RoHS Compliant
- EU ELV Compliant
- Connector System Wire-to-Component
- Accessory Type Cover - Cable Exit
- Cable Exit Angle 180
- Sealable Yes
- Strain Relief With

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

PROTECTIVE COVER Schutzkappe
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Connector System** Wire-to-Component
- Accessory Type** Cover - Cable Exit
- Sealable** Yes
- Strain Relief** With

Configuration Features

- Number of Positions** 1

Body Features

- Cable Exit Angle** 180
- Color** Orange
- Material** PA GF

Dimensions

- Cable Bundle Diameter** 10.2 mm [.401 in]

Usage Conditions

- Operating Temperature Range** -40 – 140 °C [-40 – 284 °F]

Industry Standards

- UL Flammability Rating** UL 94-HB

Packaging Features

- Packaging Method** Carton
- Packaging Quantity** 500

Other

- Serviceable** No

Statement of Compliance

