

M17-DEVH-SCR/BAY-ANG-TRN-21x21-2.7



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 200 6100
Specification	M17-DEVH-SCR/BAY-ANG-TRN-21x21-2.7
HARTING eCatalogue	https://harting.com/21172006100

Identification

Category	Hoods / Housings
Series	Circular connectors M17
Type of hood/housing	Panel feed through housing
Description of hood/housing	Front mounting

Version

Size	M17
Shielding	Shielded
Version	Angled entry
Locking type	Screw locking Toggle locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66 / IP67 screwed / locked condition

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

Commercial data

Packaging size	1
Net weight	65.136 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140568471
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405