



Product Search Assistant (β version)

We suggest candidate products with similar specifications

in the same size or small size

Small size

High capacity

High withstand voltage

High temperature response

Focus on DC bias characteristics

Reference information

Packaging code	specification	Minimum order unit
D	φ 180 mm paper tape	10000
J	φ 330mm paper tape	50000
W	Dia. 180 mm paper tape (W8P1 *) * Width: 8 mm, pocket pitch: 1 mm	20000

Mass (typical value)	
1 piece	1.6 mg
φ 180 mm reel	118g

Characteristic data graph

Frequency characteristics | Z |

■GCM155R11H471KA01, DC0V, 20degC

画像保存

CSV

詳細設定

Frequency characteristic R

■GCM155R11H471KA01, DC0V, 20degC

画像保存

CSV

詳細設定

DC bias characteristics

■GCM155R11H471KA01, capacitance, 20.0 deg C, AC 1.0 V rms

AC voltage characteristics

■GCM155R11H471KA01, capacitance, DC0V, 20.0degC

