


 [Live Product Chat](#)



✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Connector
- Jack
- Standard
- Terminate To Coaxial Cable
- Coupler Style = Quick Connect/Disconnect

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- None Available

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

- Product Type = Connector
- Gender = Jack
- Connector Series = Standard
- Body Style = Straight
- Grade = Commercial
- Panel Thickness (mm [in]) = 2.36 [0.093]
- Dielectric Material = TFE Fluorocarbon
- Solder Pot = With

- Panel Attachment = With
- Panel Attachment Style = Front Mount
- Panel Attachment Method = Bulkhead

- Connector Impedance (Ω) = 50
- Environmental Seal = Without

- Coupler Style = Quick Connect/Disconnect
- Pin Protection = Without
- Solder Lug = Without
- Body Plating = Gold per MIL-G-45204, Type II, Grade C, Class 1
- Terminal Style = Solder Pot

- Center Contact Plating = Gold over Copper
- Contacts = With

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

- Terminate To = Coaxial Cable

- Brand = AMP