

## Specification Sheet

Part Number: HDM250HIRC2



Mount and tie combination makes it easy to service bundles in the field. Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.

Eliminates the needs for multiple sized fix diameter clamps.

Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.25", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 100/pkg

Article Number 151-00437

Type HDM25

Color Black (BK)

Quantity Per bag

Product Description These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

Short Description Standard Torque Cable Tie Mount, Mtg Hole Dia. 0.25", Max Torque 115.0 in lbs, PA66HIRHSUV, Black, 100/pkg

|                  |                      |
|------------------|----------------------|
| Global Part Name | HDM25-PA66HIRHSUV-BK |
|------------------|----------------------|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 1.41 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Length L (Metric) | 36.3 |
|-------------------|------|

|                 |                          |
|-----------------|--------------------------|
| Fixation Method | Screw Mounting and Rivet |
|-----------------|--------------------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.75 |
|--------------------|------|

|                  |      |
|------------------|------|
| Width W (Metric) | 19.3 |
|------------------|------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 0.66 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Height H (Metric) | 16.7 |
|-------------------|------|

|                                |     |
|--------------------------------|-----|
| Cable Tie Width Max (Imperial) | 0.5 |
|--------------------------------|-----|

|                              |      |
|------------------------------|------|
| Cable Tie Width Max (Metric) | 12.7 |
|------------------------------|------|

|                                     |      |
|-------------------------------------|------|
| Mounting Hole Diameter D (Imperial) | 0.25 |
|-------------------------------------|------|

|                                   |        |
|-----------------------------------|--------|
| Mounting Hole Diameter D (Metric) | 6.2 mm |
|-----------------------------------|--------|

|                                         |      |
|-----------------------------------------|------|
| Mounting Hole Diameter D Min (Imperial) | 0.25 |
|-----------------------------------------|------|

|                                         |      |
|-----------------------------------------|------|
| Mounting Hole Diameter D Max (Imperial) | 0.25 |
|-----------------------------------------|------|

|                                       |     |
|---------------------------------------|-----|
| Mounting Hole Diameter D Max (Metric) | 6.2 |
|---------------------------------------|-----|

|                        |        |
|------------------------|--------|
| Stud Diameter (Metric) | 6.2 mm |
|------------------------|--------|

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| Stud Diameter (Imperial)     | 0.25                                                                     |
| Material                     | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut            | PA66HIRHSUV                                                              |
| Flammability                 | UL 94 HB                                                                 |
| Halogen Free                 | Yes                                                                      |
| UV Resistant (Yes/No)        | Yes                                                                      |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                        |
| Maximum Torque (kgf-cm)      | 132.5                                                                    |
| Maximum Torque (lbf-ft)      | 9.583                                                                    |
| Reach Compliant (Article 33) | Yes                                                                      |
| ROHS Compliant               | Yes                                                                      |
| Package Quantity (Imperial)  | 100                                                                      |
| Package Quantity (Metric)    | 100                                                                      |
| Customs Number               | 3926909988                                                               |

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)