

Part Number : [1300700019](#)

Product Description : BradPower D-Size (1 3/8"-M35) Female Closure Cap, Internal Threads, 38.35mm Diameter

Series Number : 130070

Status : Active

Product Category : Industrial Accessories

Engineering Part Number : 55-0298




Documents and Resources

Drawings

[1300700019 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Accessories
Series	130070
Description	BradPower D-Size (1 3/8"-M35) Female Closure Cap, Internal Threads, 38.35mm Diameter
IP Rating	N/A
Product Name	BradPower D-Size
Type	Closure Cap
UPC	78678855155

Physical

Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Component	Anodized Aluminum
Net Weight	98.110/g
Temperature Range - Operating	-20° to +90°C

This document was generated on May 22, 2026