

Extruded Self-Retaining LED Mounts

Ordering Information For ERC, ERB & ERM-1 Series

"L" DIMENSIONS	ERB	ERC	ERM
.040-.075 (1.0 -1.9)	U	U	U
.080-.150 (2.0-3.8)	V	V	V
.155-.230 (4.0-5.8)	W	W	W
.235-.310 (6.0-7.9)	X	X	X
.315-.380 (8.0-9.7)	Y	Y	Y
.385-.495 (9.8-12.6)	Z	Z	Z
.500-.750 (12.7-19.1)	ZZZ	ZZZ	ZZZ
.755-1.250 (19.2-31.8)	ZZZZ	ZZZZ	ZZZZ

EXAMPLES:
ERB-400 is price code Z
ERC-050 is price code U
ERM-150 is price code W



ERC, ERB & ERM-1 Series Metric Conversion

mm	Inch	Part No.	Price Code	mm	Inch	Part No.	Price Code	mm	Inch	Part No.	Price Code
1	.039	ERB-1mm	V	1	.039	ERC-1mm	V	1	.039	ERM-1mm	V
2	.079	ERB-2mm	V	2	.079	ERC-2mm	V	2	.079	ERM-2mm	V
3	.118	ERB-3mm	W	3	.118	ERC-3mm	W	3	.118	ERM-3mm	W
4	.158	ERB-4mm	X	4	.158	ERC-4mm	X	4	.158	ERM-4mm	X
5	.197	ERB-5mm	X	5	.197	ERC-5mm	X	5	.197	ERM-5mm	X
6	.236	ERB-6mm	Y	6	.236	ERC-6mm	Y	6	.236	ERM-6mm	Y
7	.276	ERB-7mm	Y	7	.276	ERC-7mm	Y	7	.276	ERM-7mm	Y
8	.315	ERB-8mm	Z	8	.315	ERC-8mm	Z	8	.315	ERM-8mm	Z
9	.354	ERB-9mm	Z	9	.354	ERC-9mm	Z	9	.354	ERM-9mm	Z
10	.394	ERB-10mm	ZZ	10	.394	ERC-10mm	ZZ	10	.394	ERM-10mm	ZZ
11	.433	ERB-11mm	ZZ	11	.433	ERC-11mm	ZZ	11	.433	ERM-11mm	ZZ
12	.472	ERB-12mm	ZZ	12	.472	ERC-12mm	ZZ	12	.472	ERM-12mm	ZZ
13	.512	ERB-13mm	ZZZ	13	.512	ERC-13mm	ZZZ	13	.512	ERM-13mm	ZZZ
14	.551	ERB-14mm	ZZZ	14	.551	ERC-14mm	ZZZ	14	.551	ERM-14mm	ZZZ
15	.591	ERB-15mm	ZZZ	15	.591	ERC-15mm	ZZZ	15	.591	ERM-15mm	ZZZ
16	.630	ERB-16mm	ZZZ	16	.630	ERC-16mm	ZZZ	16	.630	ERM-16mm	ZZZ
17	.669	ERB-17mm	ZZZ	17	.669	ERC-17mm	ZZZ	17	.669	ERM-17mm	ZZZ
18	.709	ERB-18mm	ZZZ	18	.709	ERC-18mm	ZZZ	18	.709	ERM-18mm	ZZZ
19	.748	ERB-19mm	ZZZ	19	.748	ERC-19mm	ZZZ	19	.748	ERM-19mm	ZZZ
20	.787	ERB-20mm	ZZZZ	20	.787	ERC-20mm	ZZZZ	20	.787	ERM-20mm	ZZZZ
21	.827	ERB-21mm	ZZZZ	21	.827	ERC-21mm	ZZZZ	21	.827	ERM-21mm	ZZZZ
22	.868	ERB-22mm	ZZZZ	22	.868	ERC-22mm	ZZZZ	22	.868	ERM-22mm	ZZZZ
23	.906	ERB-23mm	ZZZZ	23	.906	ERC-23mm	ZZZZ	23	.906	ERM-23mm	ZZZZ
24	.945	ERB-24mm	ZZZZ	24	.945	ERC-24mm	ZZZZ	24	.945	ERM-24mm	ZZZZ
25	.984	ERB-25mm	ZZZZ	25	.984	ERC-25mm	ZZZZ	25	.984	ERM-25mm	ZZZZ
26	1.024	ERB-26mm	ZZZZ	26	1.024	ERC-26mm	ZZZZ	26	1.024	ERM-26mm	ZZZZ