







| LOC |  | DIST |     | REVISIONS   |      |     |      |
|-----|--|------|-----|-------------|------|-----|------|
|     |  | P    | LTR | DESCRIPTION | DATE | DWN | APVD |
|     |  |      |     | -           | -    | -   | -    |
|     |  |      |     |             |      |     |      |
|     |  |      |     |             |      |     |      |
|     |  |      |     |             |      |     |      |



- △ HOUSING: THERMOPLASTIC, COLOR BLACK, FLAMMABILITY RATING UL 94 V-0.
- △ THIS ASSEMBLY TO MATE WITH TEC PART NUMBER 2212305-1.
3. RECOMMENDED SHOULDER SCREW:  
2212056, FLOAT MOUNT  
2212055, FIXED MOUNT
- △ RECOMMENDED PANEL CUTOUT FOR FRONT PANEL MOUNT APPLICATION.  
RECOMMENDED PANEL THICKNESS 1.5 TO 1.78.
- △ DATE CODE AND PART NUMBER IN APPROXIMATE AREA SHOWN.



SCALE 1:1

FULLY MATED ASSEMBLIES △

|                                                      |  |  |  |                  |            |           |      |
|------------------------------------------------------|--|--|--|------------------|------------|-----------|------|
| CONNECTOR, SOCKET, FORGE 4x#0,0x#4,0x#8,0x#12,2x#22, |  |  |  | 2212307-1        |            |           |      |
| DESCRIPTION                                          |  |  |  | PART NO.         |            |           |      |
| THIS DRAWING IS A CONTROLLED DOCUMENT.               |  |  |  | DWN              | R. TREA    | 11FEB2015 |      |
| DIMENSIONS:                                          |  |  |  | CHK              | E. WICKERS | 11FEB2015 |      |
| mm                                                   |  |  |  | APVD             | D. ORRIS   | 11FEB2015 | NAME |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:               |  |  |  | PRODUCT SPEC     |            |           |      |
| 0 PLC ±N/A                                           |  |  |  | 108-2323         |            |           |      |
| 1 PLC ±N/A                                           |  |  |  | APPLICATION SPEC |            |           |      |
| 2 PLC ±0.25                                          |  |  |  | 114-13299        |            |           |      |
| 3 PLC ±0.13                                          |  |  |  | WEIGHT           |            |           |      |
| 4 PLC ±N/A                                           |  |  |  | Customer Drawing |            |           |      |
| ANGLES                                               |  |  |  | SCALE 2:1        |            |           |      |
| FINISH                                               |  |  |  | SHEET 1 OF 2     |            |           |      |
| MATERIAL                                             |  |  |  | REV 1            |            |           |      |

THIS PRINT IS  
**PRELIMINARY**  
UNQUALIFIED PRODUCT  
CONTACT PRODUCT ENGINEERING  
BEFORE USING THIS PRINT

CONNECTOR SOCKET, FORGE  
4x#0,0x#4,0x#8,0x#12,2x#22  
CONFIGURATION

SIZE CAGE CODE DRAWING NO  
A100779C=2212307

RESTRICTED TO  
-

