## Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
  - Accessory
  - M5
  - Guided M8
  - M8
  - M10.5
  - M12 (A)
  - M12 (B)
  - M12 (D)
  - M12 (I)
  - M12 (K)
  - M12 (L)
  - M12 (S)
  - M12 (T)
  - M12 (X)
  - M23
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





# M12A05ML-12AFL-SDA05

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: N/A
- Shielded: Metal, Non-shielded
- Jacket Material: PVC
- Certificate: UL1977, UL2238, UL1863

You must login first for view the price


Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

## Mating Pair & Accessories

Connector Type ▾ Search



| M Series,... | M Series,... | M Series, M12, A... | M Series, M12, A... | M Series, M12, A... | M Series, M12, A... |
|---|---|---|---|---|---|
| CAP-WBDMSMA2 -40°C ~ +105°C | IA-A05F-A05F-... -20°C ~ +85°C | LM12A-05BFFM-... -20°C ~ +80°C | LM12A-05BFFM-... -20°C ~ +80°C | LM12A-05BFFM-... -20°C ~ +80°C | LM12A-05BFFM-... -20°C ~ +80°C |
| − 0 + | − 0 + | − 0 + | − 0 + | − 0 + | − 0 + |

Add to Cart | Inquiry

**Specifications** | Download / CAD

| | |
|---|---|
| Nominal Current<br>**4A** | Connector Type<br>**Overmolded** |
| Shielded<br>**Metal, Non-shielded** | No. of Contacts<br>**05** |
| Connector Gender<br>**Male** | Backshell<br>**Straight** |
| Mating Style<br>**Screw Thread** | IP Rating<br>**IP68** |
| Assembly Style<br>**N/A** | |

More Options

### People Also Bought



M12A05ML-12AFL-... | RCP-5SPFFP-... | AB-BB03ML-BBFL-... | DD-12AFMM-QL8D10 | AB-BB03ML-BBML-...



Downloaded from Arrow.com.