



Part Number : 1301380082

Series Number : 130138

Product Category : Power Distribution

Product Description : Watertite Multiple Outlet Pendant Box, GFCI, (1)NEMA 5-20 Duplex with Flip Lids, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip

Status : Active

Engineering Number : 70W33M123GF

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Relevant

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution
Series	130138

Description	Watertite Multiple Outlet Pendant Box, GFCI, (1)NEMA 5-20 Duplex with Flip Lids, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-20
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite
Type	Multiple Outlet Box
UPC	78678828312

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	No
Voltage - Maximum	120V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	4.57m (15.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Number of Receptacles	1
Packaging Type	Carton
Receptacle Type	Duplex