Part Number : 1300680099
Product Description : BradPower D-Size (1 3/8"–M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"–M35) Drop, Black
Series Number : 130068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : TC40C40-200G



Documents and Resources

Drawings

1300680099_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130068
Description	BradPower D-Size (1 3/8"–M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"–M35) Drop, Black
IP Rating	IP67
Product Name	BradPower D-Size
Type	Power Tap Tee
UPC	78172536310

Agency

UL	E258922

Electrical

Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Physical

Drop Connector	BradPower D-Size (1 3/8"–M35)
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	BradPower D-Size (1 3/8"–M35)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A

Downloaded from Arrow.com.

Material - Connector Body	PVC
Material - Coupling Nut	Anodized Aluminum
Net Weight	458.000/g
Poles	4
Right Trunk Connector	BradPower D-Size (1 3/8"–M35)
Right Trunk Gender	Male
Temperature Range - Operating	-20° to +90°C

Downloaded from Arrow.com.