

Description

MG Chemicals line of swabs are offered in chamois, cotton, and foam tips. The swabs are designed with a round, tapered, or rectangular tip shape that are suited for all general and precision cleaning applications.





Applications & Usages





The chamois are ideal for cleaning sensitive tape, audio, and optical heads. The cotton and foam swabs are designed for cleaning equipment, removing flux residues, applying adhesives, and absorbing chemical residues.

Benefits and Features

- **ESD safe**—Cat No. 812AS
- **Non-abrasive**
- **100 ppi medical grade head**—Cat No. 812 and 8113
- **Low to zero lint and residue free**
- **Can be used with IPA (isopropyl alcohol) or DI (distilled) water**

Product Details

<i>Cat No.</i>	<i>Overall Length</i>	<i>Tip Length</i>	<i>Handle Length</i>	<i>Handle Material</i>	<i>Tip End</i>	<i>Quantity per Bag</i>
Chamois Swab						
 810-15	4"	0.9"	3.2"	Plastic	Single	15
810-50	4"	0.9"	3.2"	Plastic	Single	50
810D-15	5"	0.9"	3.2"	Plastic	Double	15
810D-50	5"	0.9"	3.2"	Plastic	Double	50
Double Headed Cotton Swab						
 811-100	6"	0.5"	5"	Wood	Double	100
Foam Over Cotton Swab						
 812-10	6"	0.5"	5.5"	Wood	Single	10
812-50	6"	0.5"	5.5"	Wood	Single	50
812-250	6"	0.5"	5.5"	Wood	Single	250
812-1000	6"	0.5"	5.5"	Wood	Single	1 000
Anti-Static Foam Over Cotton Swab						
 812AS-10	6"	0.8"	5.3"	Wood	Single	10

Cat No.	Overall Length	Tip Length	Handle Length	Handle Material	Tip End	Quantity per Bag	
Foam Swab							
	813-10	6"	0.6"	5.5"	Wood	Single	10
	813-50	6"	0.6"	5.5"	Wood	Single	50
	813-250	6"	0.6"	5.5"	Wood	Single	250
	813-1000	6"	0.6"	5.5"	Wood	Single	1 000
Rectangular Foam Swab							
	814-10	5.5"	0.9"	4.5"	Polypropylene	Single	10
	814-50	5.5"	0.9"	4.5"	Polypropylene	Single	50
	814-250	5.5"	0.9"	4.5"	Polypropylene	Single	250
	814-1000	5.5"	0.9"	4.5"	Polypropylene	Single	1 000
Tapered Cotton Swab							
	8112A-100	5.875"	0.5"	5.812"	Wood	Single	100
Cotton Tipped Application Swab							
	8113-25	3.2"	0.4"	2.5"	Polypropylene	Double	25
	8113-25000	3.2"	0.4"	2.5"	Polypropylene	Double	25 000

Note: All lengths are an approximation.

Technical Support

Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Phone: +(1) 800-340-0772 (Canada, Mexico & USA)

+ (1) 905-331-1396 (International)

Fax: +(1) 905-331-2862 or +(1) 800-340-0773

Mailing address: **Manufacturing & Support**
1210 Corporate Drive
Burlington, Ontario, Canada
L7L 5R6

Head Office
9347-193rd Street
Surrey, British Columbia, Canada
V4N 4E7

Disclaimer

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. *M.G. Chemicals Ltd.* does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.