



TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

+ CONNECTORS

SOLID STATE LIGHTING CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

6POS 3.5MM TOP ENTRY SCREWLESS CONN.

Poke In Wire Connector Modular

1-2834011-6

TE Internal Number: 1-2834011-6

EU RoHS Compliant

EU ELV Compliant

Connector Style Receptacle

Contact Current Rating (Max) (A) 6

Sealable No

Mounting Angle Vertical

Wire/Cable Size (AWG) 20 – 14



PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

3.5mm Top Entry Modular Screwless Conn

PDF

English

Catalog Pages/Data Sheets

Modular Screwless Terminal Blocks Flyer

PDF

English

Product Specifications

Product Specification

Product Specification For 3.5mm Top Entry Screwless Connector

PDF

English

Application Specification

3.5mm Top Entry Modular Screwless Conn.

PDF

English

Qualification Test Report

TESE REPORT FOR 3.5mm Top Entry Screwless Conn.

PDF

English

Instruction Sheets

Instruction Sheet (non U.S.)

3.5mm Top Entry Modular Screwless Connector

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Receptacle**Sealable** No**Connector & Contact Terminates To** Printed Circuit Board**Product Type** Connector**Connector Type** Connector Assembly

Electrical Characteristics

Operating Voltage (VAC) 300

Contact Features

Contact Current Rating (Max) (A) 6**Contact Termination Area Plating Material** Tin-Lead over Nickel**Contact Termination Area Plating Finish** Matte

Termination Features

Termination Method to PC Board Through Hole

Mechanical Attachment

Mounting Angle Vertical

Dimensions

Wire/Cable Size (AWG) 20 – 14

Operation/Application

SMT Compatible No

Industry Standards

Agency/Standard UL

Packaging Features

Packaging Method Box & Carton

Statement of Compliance

Statement of Compliance

PDF