Part Number : 731712631
Product Description : Mini-BNC Jack, Straight, Crimp, Bulkhead, RG-179 Cable, Brass Body, Nickel (Ni) Plated, with Jam Nut and Lockwasher, Tray, 75 Ohms
Series Number : 73180
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

731712631_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/30/2017 (7 July 2017)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73180
Description	Mini-BNC Jack, Straight, Crimp, Bulkhead, RG-179 Cable, Brass Body, Nickel (Ni) Plated, with Jam Nut and Lockwasher, Tray, 75 Ohms
Application	RF
Product Name	Mini-BNC
Style	Cable
Type	Subminiature
UPC	822350399852

Electrical

Frequency	3 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 300 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Jack
Keying to Mating Part	N/A
Net Weight	4.939/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	N/A

Downloaded from Arrow.com.

Reverse Polar	No
Wire/Cable Type	RG-179

Solder Process Data

Lead-Free Process Capability	N/A

Downloaded from Arrow.com.