


Technical data sheet

Article number:
118-04701

T18ROS



Product Group	Cable ties for thin-walled bundles
Product Family	OS-Series
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK)
Application Range	Indoor Use
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	20.0 mm
Bundle Ø min.	1.6 mm
Flammability	UL 94 V2
Halogen-free	Yes
Height (H)	1.0 mm
Length (L)	100.0 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +105 °C
Package Content packed in	pack
Pack Cont.	500 pcs.
Releasable Closure (Yes/No)	No
Thickness (T)	1.0 mm
Toothing (Serration)	Outside Serrated
Variant	Outside Serrated
Weight/Unit	0.000267 kg
Width (W)	2.5 mm

