

4





3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-14-013215	4SEP14	SE	BW
	D2	REVISED PER ECR-19-018072	29NOV2019	SS	TD
	D3	REVISED PER ECR-25-241690	18APR2025	AG	JS
	D4	REVISED PER ECR-25-242035	21APR2025	AG	JS



NOTES:

1. GENERAL TOLERANCE ±0.3mm , ±3°
2. TE TRADE MARK, C/V MARK MUST BE CLEAR AND LEGIBLE
3. USE CONTACT PART NO. 170324-1, 170325-1, 170326-1.

	NAT	PA66 (V-0)	1-368602-1
OBSOLETE	BLUE	PA66 (V-2)	368602-2
	NAT	PA66 (V-2)	368602-1
	COLOR	MATERIAL	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SE JUNG														
DIMENSIONS: mm		CHK BH CHO														
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD BW KANG	NAME 187 SERIES 1P P-LOCK(MKII) REC HSG WITH PROTECTOR AND TAB GUIDE													
<table border="1"> <tr> <td>0 PLC</td> <td>±</td> </tr> <tr> <td>1 PLC</td> <td>±0.1</td> </tr> <tr> <td>2 PLC</td> <td>±0.01</td> </tr> <tr> <td>3 PLC</td> <td>±0.001</td> </tr> <tr> <td>4 PLC</td> <td>±0.0001</td> </tr> </table>		0 PLC	±	1 PLC	±0.1	2 PLC	±0.01	3 PLC	±0.001	4 PLC	±0.0001	PRODUCT SPEC 108-61237	SIZE A3	CAGE CODE 00779	DRAWING NO C=368602	RESTRICTED TO
0 PLC	±															
1 PLC	±0.1															
2 PLC	±0.01															
3 PLC	±0.001															
4 PLC	±0.0001															
MATERIAL SEE NOTE		APPLICATION SPEC 114-5041	SCALE 4:1		SHEET 1 OF 1	REV D4										
FINISH		WEIGHT	CUSTOMER DRAWING													