HellermannTyton

Technical data sheet

Article number:
115-40300 REZ300

Product Group	Cable ties inside serrated with one-hand release mechanism
Product Family	REZ-Series
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)

Bundle Ø max.	80.0 mm
Bundle Ø min.	16.0 mm
Flammability	UL 94 V2
Length (L)	305 mm
Min.Tensile Strength	135 N
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Package Content packed in	pack
Releasable Closure (Yes/No)	Yes
Thickness (T)	1.4 mm
UV-Stabilised	No
Variant	Inside Serrated
Weight/Unit	0.002448 kg
Width (W)	4.7 mm

RoHS

created on 18. September 2026, 7:18 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.