

NEED HELP?
Contact Customer Service
 (800) 627 - 7100

CONTACT US

AMPHENOL RF PART NUMBER

3FA1-NASJ-C01E6

FAKRA Sealed Straight Single Jack, With Clip, 50 Ohm, RG-174, RG-188 RG-316, DACAR 462

FIND STOCK & BUY NOW



PRODUCT OVERVIEW

RF Connector, FAKRA Sealed Straight Single Jack, With Clip, 50 Ohm, RG-174, RG-188, RG-316, DACAR 462

Product Type	Connectors
Product Series	FAKRA
Status	Active

DOWNLOADS

Please [contact us](#) for additional product information.

PRODUCT SPECIFICATIONS

Brand	Amphenol RF
Gender	Jack
Orientation	Straight
Termination Style	Cable - Crimp
Impedance (Ohms)	50
Body Finish	Nickel/Tin
Body Material	Phosphor Bronze
Contact Finish	Gold
Contact Material	Phosphor Bronze
Contact Termination Style	Solder
Insulator Material	PBT
Cable Group	C01
Cable Type	DACAR 462, RG-174, RG-188, RG-316
Coupling Mechanism	Keyed
IP Rating	IP67
Max Frequency (GHz)	3
Polarity	Standard
Min. Temp. (Celsius)	-40
Max. Temp. (Celsius)	105
Mating Cycles	100
FAKRA Keycode	A

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant - View Certificate
-------------	--

Additional compliance information is available in our [Product Compliance Center](#).

ADD TO COMPARE

[AMPHENOL RF](#)

[QUICK LINKS](#)

[CONTACT US](#)

[FOLLOW US](#)



[NEWSLETTER](#)

Copyright © 2014 Amphenol RF. All Rights Reserved.

[Copyright](#) | [Terms & Conditions](#) | [Privacy Policy](#) | [Logos](#) | [Amphenol.com](#)

LMR® is a registered trademark of Times Microwave Systems