

[Request more info](#)

Part Number : 5973609207F

[C17824](#)[Surface Mount LED Selector Guide](#)

This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	597
Configuration	POWER PLSS 4 SMT Leds
Description	Smd Led PLCC4 Blue 30ma 7"Reel
Package Options	2000 Pcs Per Reel
Viewing Angle	120°

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	50mA
Solder Temperature	260°C for 5 sec.
Operating Temperature	-40 to 110°C
Storage Temperature	-40 to 110°C

Operating Characteristics

Color	Blue
Peak Wave Length	464
Luminous Intensity Min	280
Luminous Intensity Typical	450
Luminous Intensity Max	710
Forward Voltage Min	2.90
Forward Voltage Typical	3.30
Forward Voltage Max	3.80
Test Current mA	30mA
Dominant Wavelength Min	463
Dominant Wavelength Typical	469