

1.4kW Single-Phase Local Metered PDU, 120V Outlets (16 5-15R), 5-15P, 15 ft. (4.57 m) Cord, 0U Vertical, 48 in.

MODEL NUMBER: PDUMV15



Features

- 15A single phase 120V Local Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA 5-15P 15A 120V input plug with 15-ft. (4.57 m) line cord
- 0U 48in / 122cm vertical rackmount format installs using no rack spaces
- 16 NEMA 5-15R outlets
- Includes 15A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

OVERVIEW	
UPC Code	037332132536
PDU Type	Local Metered
INPUT	
Input Phase	Single-Phase
PDU Input Voltage	120
Recommended Electrical Service	Single-phase 15A 120V service
Maximum Input Amps	12

Highlights

- Local Metered single phase 12A 120V 0U 48in / 122cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA 5-15P input plug
- 16 NEMA 5-15R outlets
- Toolless button mount and bolt-down bracket installation hardware included

Package Includes

- PDUMV15 Local Metered Vertical PDU
- Mounting hardware and spare mounting buttons
- Owner's manual with warranty information

Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	1.44kW (120V) / 12A total capacity; 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) 5-15R
Output Nominal Voltage	120V
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with transparent switch cover
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Metal
Form Factors Supported	Vertical (0U) mounting in rack enclosures
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	51.77 x 3.43 x 2.40
Shipping Dimensions (hwd / cm)	131.50 x 8.71 x 6.10
Shipping Weight (lbs.)	4.43
Shipping Weight (kg)	2.01
Unit Dimensions (hwd / in.)	48.470 x 1.500 x 1.640
Unit Dimensions (hwd / cm)	123.1 x 3.81 x 4.2
Unit Weight (lbs.)	3.74
Unit Weight (kg)	1.70
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-22° to 122°F (-30° to 50°C)
Relative Humidity	5% to 95% non-condensing
Operating Elevation (ft.)	0-10,000

Operating Elevation (m)	0-3000
STANDARDS & COMPLIANCE	
Product Certifications	RETIE (Colombia); NOM (Mexico); UL 60950-1
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty