

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

CATALOG LISTING

YA-1R5435242-A2

SWITCH - BASIC

YA-1R5435242-A2

PAGE 1 OF 1

RELEASE NO.	PR-5263	REPLACES
-------------	---------	----------

DRAWING
NUMBER

ISSUE 3

REVISIONS

A	CO- 73287-J
J A L	
22 NOV 93	


B C093346
DLT
31 AUG 98

FORMTEK

FO-52848-A

DRAWN

GI H	24 SEPT 75	CHECK	USD	75 SEP 75	CHECK	75	CHECK




NOTES

**▲ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .168 MAX DIA ON 1.000±.002 CENTERS
2-SWITCH WILL WITHSTAND TEMPERATURE OF 250 ° F**

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — — 9 OZ MAX

RELEASE FORCE - - - - - 4 OZ MIN

DIFFERENTIAL TRAVEL--.0025--.0040

OVERTRAVEL— — — — — .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

UL LISTED - FILE E12252

CODE L65 15A-125, 250 OR 480 VAC
1/2HP-125 VAC; 1HP-250 VAC

L288
L299
L306



16A 250V T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/04		
ONE PLACE	X,X	0.4/0.16	X,X	0.81/0.3
TWO PLACES	X,XX	0.15/0.006	X,XX	0.38/0.015
THREE PLACES			X,XXX	0.13/0.005
ANGLES				

DESIGN UNITS ☐ METRIC

US CUSTOMARY

WEIGHT .065 LB

GGLH	24 SEPT 75	CHECK	LSD	25 SEP 75	CHECK	CNT	25 SEP 75
------	------------	-------	-----	-----------	-------	-----	-----------