





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/7/19	
A		ADDED PACKING	4/12/22	WX/YC



PECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 2.0 Amp

Contact resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



PACKAGED ON TAPE & REEL

Positions: 04 thru 80

A = .079 [2.00] x No. of Positions + .016 [0.40]

B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN	LH	10/7/19
CHECKED	EY	10/7/19
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.079 [2.00] DUAL ROW ROWRECEPTACLE STRIP,
.157 [4.00] HEIGHT, GOLD PLATED, SMT TYPE

SIZE X PART NO. 2RS2LA-XX-G-SMT-PP-T/R REV. A

REF: S00111C SCALE: NTS SHEET 1 OF 2

6

5

4

3

2

1




APPROVED: _____

DATE: _____ TITLE: _____

Rev AWO # Description Date Appr

SEE SHT 1 OF 2 FOR REVISION

FEED DIRECTION



Notes:

1. Packing Conforms EIA-481-B Standards.
2. 10 sprocket hole pitch cumulative
3. Carrier camber is within 1mm in 250mm.
4. Material: Nature Polystyrene.
5. Packing length per 13" Reel: 12.48 Meters.
6. Component load per 13" Reel: 1000+40 PCS.

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ϕ .X ± .10
.XX ± .020	ϕ .XX ± .015
.XXX ± .015	ϕ .XXX ± .010

DRAWN LH 10/7/19

CHECKED EY 10/7/19

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

**ADAM
TECH**909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
.079 [2.00] DUAL ROW ROW RECEPTACLE STRIP,
.157 [4.00] HEIGHT, GOLD PLATED, SMT TYPE

SIZE X PART NO. 2RS2LA-XX-G-SMT-PP-T/R REV. A

REF: S00111C SCALE: NTS SHEET 2 OF 2

6

5

4

3

2

1