


OGA DIAGONAL: 16.40 [416.59]
VA DIAGONAL: 15.68 [398.29]
PA DIAGONAL: 14.79 [375.72]

THIS PRODUCT IS MANUFACTURED IN ACCORDANCE
WITH THE CURRENT CLEARTEK II CAPACITIVE
TOUCH SCREEN SPECIFICATION (DOCUMENT 23655)



TOP LEVEL NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH
17-8031-203	FFC	4.27" [108.46]	AG500
17-8031-204	FFC	6.00" [152.40]	AG500
17-8031-205	FFC	8.00" [203.20]	AG500
17-8031-206	NOV	SEE DWG	AG500
17-8031-217	USB	4.27" [108.46]	AG500
17-8031-219	USB	6.00" [152.40]	AG500
17-8031-221	SER	4.27" [108.46]	AG500
17-8031-223	SER	6.00" [152.40]	AG500
17-8031-225	USB	8.00" [203.20]	AG500
17-8031-227	SER	8.00" [203.20]	AG500
17-8031-218	USB R	4.27" [108.46]	AG500
17-8031-226	USB R	8.00" [203.20]	AG500
17-8031-230	HID M	8.00" [203.20]	AG500

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 638.98 ± 10%
2. 5 PIN AMP CONNECTOR LATCH STYLE HOUSING P/N: 487526-4 TIN CONTACTS P/N: 2-487406-4 HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHLD
4	UL
5	UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	± .03 [.76]
.XX	± .015 [.38]
ANGLES	± 1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE	1 = 1



3M TOUCH SYSTEMS
METHUEN, MA
USA
© COPYRIGHT 2005
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

DRAWN: K. CROWLEY 9/05

04	REVISED PER CO 028873	5/08	SEB
03	REVISED PER CO 028687	2/08	ACM
02	REVISED PER CO 026945	2/07	MDS
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING 17-803X-2XX			
CAD FORMAT		SHEET	
AUTOCAD		1 OF 1	
SIZE		DOCUMENT NO.	
C		28138-MKT	
			REV
			04