



Part Number : [50579010](#)
Product Description : SL Crimp Housing, Single Row, Version A, Non-polarized, 10 Circuits, Black
Series Number : 70066
Status : Active
Product Category : Connector Housings
Engineering Part Number : 70066-0009



Documents and Resources

Drawings

[050579010 sd.pdf](#)
[PK-70066-100-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-70058-001.pdf](#)
[PS-70400-001.pdf](#)
[PS-71851-001.pdf](#)
[TS-70058-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	70066
Description	SL Crimp Housing, Single Row, Version A, Non-polarized, 10 Circuits, Black
Application	Signal, Wire-to-Board
Comments	Version A
Product Name	SL
UPC	800753578227

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No

Keying to Mating Part	No
Lock to Mating Part	No
Material - Resin	Polyester
Net Weight	0.071/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 Vertical Breakaway Headers with Friction Lock	<u>42375</u>
KK 254 Right-Angle Surface Mount Compatible Breakaway Headers	<u>42377</u>
C-Grid Vertical Dual Row Breakaway Headers	<u>70280</u>
C-Grid Vertical Dual Row Breakaway Headers with Retention Pin	<u>70287</u>
SL Vertical Single Row Headers	<u>70543</u>
SL Right-Angle, Single Row, Low Profile Headers	<u>70553</u>
C-Grid Vertical, Dual Row, Surface Mount Breakaway Headers	<u>71308</u>

Use with Part(s)

Description	Part Number
SL Female Terminals	<u>70058</u>

This document was generated on May 21, 2026