

 [Live Product Chat](#)



TE Part Number: 828278-6

✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Backshell/Cable Clamp
- Cable Clamp Type = Two-Piece RFI/EMI Shield
- Straight(180°)/45° Cable Exit Angle
- Cable Insulation Diameter = 10.00 mm
- Number of Positions = 25

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings:

- [COVER FOR HD-20 25POLIG](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Backshell/Cable Clamp
- Cable Clamp Type = Two-Piece RFI/EMI Shield
- Number of Positions = 25
- Shell Size = 3
- Shielded = Yes
- Screws and Retainer Clips = Without
- Grommets = Without
- Slide Latch = Without
- Thread Size = 4-40

Body Related Features:

- Cable Exit Angle = Straight(180°)/ 45°
- Cable Insulation Diameter (mm [in]) = 10.00
[0.393]
- Cable Clamp Material = Polycarbonate
- Shield Plating = Bright Nickel over Copper
- Cover Flammability Rating = UL 94V-0

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Individual Kit
- Packaging Quantity = 50

Other:

- Brand = AMP