



Part Number : [191930139](#)
Product Description : VersaKrimp Ring
Tongue Terminal for 12-10 AWG Wire, Closed-
Braided Barrel, Stud Size 3/8" (M9), Mylar Tape
Carrier
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : C-340-38T



Documents & Resources

Drawings
[191930139_sd.pdf](#)

3D Models and Design Files
[191930139_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Mylar Tape Carrier
Comments	Type I Non-insulated; Class 1 and 2
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	800753039421

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.955/g
Packaging Type	Adhesive Tape on Reel
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	5.76mm max.
Wire Size (AWG)	10, 12

Wire Size mm ²	4.00-6.00
---------------------------	-----------

Application Tooling

Global

Description	Part Number
Perishable Tooling Spacers for tape product	<u>190270133</u>
ATP Perishable Tool Kit used in ATP Presses that Process Product on Tape	<u>190270300</u>
Mini-Mac Applicator	<u>638851000</u>

This document was generated on Mar 03, 2025