# 7-Port Portable USB 3.x (5Gbps) Mini Hub, Aluminum

MODEL NUMBER: **U360-007-AL**








Connects to the USB 3.0 port on your laptop, Ultrabook or computer to give you 7 external USB 3.0 ports.

## Description

The U360-007-AL 7-Port Portable USB 3.0 SuperSpeed Mini Hub's built-in USB cable connects to your laptop, Ultrabook or computer to provide seven available USB 3.0 ports. Just plug and play with no drivers or software needed. The included external power supply provides 5V 3A to be shared among all seven USB ports, with each port capable of providing up to 1.5A for fast charging of mobile devices. All seven ports support USB Battery Charging (BC) specification v1.2.
This portable hub supports USB 3.0 data transfer rates up to 5 Gbps—ten times faster than USB 2.0—and is backward compatible with USB 2.0 and USB 1.1 devices. The compact, lightweight aluminum case fits easily into your pocket, backpack, briefcase or laptop bag.

## Features

**Increases Your Computer's USB 3.0 Ports from 1 to 7**Expands your laptop, Ultrabook or computer's USB 3.0 port to 7 external USB 3.0 portsIncluded external power supply provides 5V 3A to be shared among all portsEach port is capable of providing up to 1.5ASupports USB Battery Charging (BC) specification v1.2

**Excellent Speed and Versatile Performance**Supports USB 3.0 data transfer rates up to 5 Gbps—10 times faster than USB 2.0Backward compatible with USB 2.0 and USB 1.1

**Take the Hub Anywhere**Compact case made from lightweight aluminumFits easily into your pocket, backpack, briefcase or laptop bagBuilt-in cable is perfect for travel

## Highlights

- USB ports can provide up to 1.5A for charging mobile devices*
- All seven ports support USB Battery Charging (BC) specification v1.2
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Plug and play—no drivers or software needed
- Fits easily into pocket, backpack, briefcase or laptop bag
- Backward compatible with USB 2.0 and USB 1.1

**When using the included external power supply*

## System Requirements

- Device with USB port (USB 3.0 port needed to achieve USB 3.0 speeds)

## Package Includes

- U360-007-AL 7-Port Portable USB 3.0 SuperSpeed Mini Hub
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 5V 3A)

# Specifications

| OVERVIEW | |
|---|---|
| UPC Code | 037332201027 |
| Product Type | Hub |
| Technology | USB 3.x |
| Host Connector | USB A (MALE) |



Downloaded from Arrow.com.

| | |
|---|---|
| **VIDEO** | |
| Number of Monitors Supported | 0 |
| Extended Mode | No |
| Mirror Mode | No |
| DisplayPort Alt Mode | No |
| **DATA** | |
| Data Ports | (7) USB A (FEMALE) |
| Data Ports Details | (7) USB-A - USB 3.2 Gen 1 (5 Gbps) |
| **INPUT** | |
| AC Power Adapter Plug(s) | NEMA 1-15P North America |
| AC Power Adapter Input Specs (V / Hz / A) | 100-240V / 50/60Hz / 0.6A |
| AC Power Adapter Output Specs (V / A) | 5V / 3A |
| AC Power Adapter Cord Length (ft.) | 5 |
| AC Power Adapter Cord Length (m) | 1.5 |
| Voltage Compatibility (VAC) | 100; 110; 120; 125; 127; 200; 208; 220; 230; 240 |
| Bus Powered | No |
| Product Length (in.) | 21.6 |
| Product Length (cm.) | 54.86 |
| Product Length (ft.) | 1.8 |
| Product Length (m) | 0.548 |
| **POWER** | |
| Power Source Type | AC Adapter |
| AC Adapter | Input: 100-240V, 50/60Hz, 0.6A; Output: 5V, 3A |
| DC Barrel Plug | OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve |
| Power Consumption (Watts) | 1.4 |
| **CONNECTIONS** | |
| Number of Ports | 7 |
| Side A - Connector 1 | USB 3.0 A (MALE) |
| Side B - Connector 1 | (7) USB 3.0 A (FEMALE) |
| Connector Plating | Nickel |
| **USER INTERFACE, ALERTS & CONTROLS** | |



Downloaded from Arrow.com.

| | |
|---|---|
| LED Indicators | White when connected and powered |
| **CHARGING** | |
| Charging Ports | USB-A: 5V 1.5A (7.5W) |
| Charging Ports Details | All seven ports support USB Battery Charging v1.2 |
| Charging Ports / Amps | (7) 1.5A |
| **PHYSICAL** | |
| Color | Black |
| Material of Construction | Aluminum |
| Cable Jacket Material | TPE |
| Cable Jacket Rating | VW-1 |
| Shipping Dimensions (hwd / in.) | 2.20 x 4.40 x 7.70 |
| Shipping Dimensions (hwd / cm) | 5.59 x 11.18 x 19.56 |
| Shipping Weight (lbs.) | 0.87 |
| Shipping Weight (kg) | 0.39 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| Unit Packaging Type | Box |
| Unit Weight (lbs.) | 0.53 |
| Unit Weight (kg) | 0.24 |
| **ENVIRONMENTAL** | |
| Operating Temperature Range | -4° to 158°F (-20° to 70°C) |
| Storage Temperature Range | 14° to 158°F (-10° to 70°C) |
| Relative Humidity | 10% to 90% RH, Non-Condensing |
| BTUs | 4.7 BTU/Hr |
| Power Provided to Connected Device(s) | 5V 1.5A (7.5W) Output per USB Port |
| **FEATURES & SPECIFICATIONS** | |
| USB Hub Ports | Yes |
| Number of USB Hub Ports | 7 |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps) |
| Driver Required | No |
| **STANDARDS & COMPLIANCE** | |
| TAA Compliant Option | N |
| External Power Supply Certifications | CE; FCC; UL; cUL; TUV; CCC; RoHS |



Downloaded from Arrow.com.

| | |
|---|---|
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| **WARRANTY & SUPPORT** | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.



Downloaded from Arrow.com.